

DVS Series

Managed Industrial Rack Mount Ethernet Switch

EN Instruction Sheet

TW 安裝說明

CN 安装说明



EN ✖ This instruction sheet only provides information on electrical specifications and general specifications.

TW ✖ 此安裝手冊只提供電氣規格與一般規格。

CN ✖ 此安裝手冊只提供电气规格與一般规格。

EN Please refer to the DELTA Industrial Ethernet Hardware Installation Guide for more detail information.


TW 更多詳細資訊請參考台達工業乙太網路硬體安裝手冊

CN 更多详细信息请参考台达工业以太网硬件安装手册

EN Managed Industrial Ethernet Switches	TW 工業級網管型乙太網路交換器	CN 网管型工业以太网交换机
● Delta DVS series Managed Industrial Rack Mount Ethernet Switch ● Protective Caps for unused RJ45 ports and fiber ports (inserted to the switch) ● USB Type A to Type B console cable ● User manual and software CD ● Instruction Sheet ● Rack bracket*4 ● M4 screw*20 ● M5 screws*6 ● T4 screw*6 and anchor screw*6 ● Rubber feet*4 ● Rubber Plug*16(Inserted to the switch)	● 台達 DVS 工業級機架式網管型乙太網路交換器 ● RJ45 與光纖保護蓋 (已安裝於機身) ● USB A 公轉 B 控制線 ● 使用手冊及產品光碟 ● 安裝說明書 ● 機架式支架 *4 ● M4 螺絲*20 ● M5 螺絲*6 ● T4 螺絲*6 與 壁虎式螺絲*6 ● 橡膠墊片*4 ● 橡皮塞*16 (已安裝於機身側邊)	● 台达 DVS 机架式网管型工业以太网交换机 ● RJ45 与光纤保护盖(已安装于机身) ● USB A 公转 B 控制线 ● 使用手册及产品光盘 ● 安装说明书 ● 机架式支架 *4 ● M4 螺丝*20 ● M5 螺丝*6 ● T4 螺丝*6 与 壁虎式螺丝*6 ● 橡胶垫片*4 ● 橡皮塞*16 (已安装于机身侧边) ● 保证卡

EN Operating Voltage	TW 操作電壓	CN 操作电压
● Input Voltage - PWR1:100-240V_{AC} (85-264V_{AC}, 88-370V_{DC}) - PWR2/PWR3:36-60V_{DC}(36-72V_{DC})	● 輸入電壓 - PWR1:100-240V_{AC} (85-264V_{AC}, 88-370V_{DC}) - PWR2/PWR3:36-60V_{DC}(36-72V_{DC})	● 输入电压 - PWR1:100-240V_{AC} (85-264V_{AC}, 88-370V_{DC}) - PWR2/PWR3:36-60V_{DC}(36-72V_{DC})

EN Ethernet interface connection definition			TW 乙太網路介面定義	CN 以太网接口定义
10/100Base-T(X)			1000Base-T	
PIN	MDI Mode	MDI-X Mode	MDI/MDI-X Mode	
1	Tx+	Rx+	TP0+	
2	Tx-	Rx-	TP0-	
3	Rx+	Tx+	TP1+	
4	n.c.	n.c.	TP2+	
5	n.c.	n.c.	TP2-	
6	Rx-	Tx-	TP1-	
7	n.c.	n.c.	TP3+	
8	n.c.	n.c.	TP3-	

EN 100/1000Base-SFP Fiber Connection		TW 100/1000Base-SFP 光纖連線	CN 100/1000Base-SFP 光纤接线
TX RX  RX TX			

EN Mechanical Characteristics	TW 實體特性	CN 实体特性
● Case IP40 metal case ● Dimension(mm) 43.66(H)x482.6(W)x275(D) ● Weight(g) 5360	● 外殼: IP40 metal case ● 尺寸(mm): 43.66(H)x482.6(W)x275(D) ● 重量(公克) : 5360	● 外壳: IP40 metal case ● 尺寸(mm): 43.66(H)x482.6(W)x275(D) ● 重量(公克) : 5360