

DVS Series

Industrial PoE+ Splitter

EN Instruction Sheet

TW 安裝說明

CN 安装说明



EN ✖ This instruction sheet only provides information on electrical specifications and general specifications.

TW ✖ 此安裝手冊只提供電氣規格與一般規格。

CN ✖ 此安裝手冊只提供电气规格與一般规格。

EN Please refer to the DELTA Industrial Ethernet Hardware Installation Guide for more detail information.

TW 更多詳細資訊請參考台達工業乙太網路硬體安裝手冊

CN 更多详细信息请参考台达工业以太网硬件安装手册

EN Package Checklist	TW 產品包裝	CN 产品包装
● Delta DVS series Industrial PoE+ Splitter ● Protective Caps for unused RJ45 ports ● Screw (M3) ● 4-pin terminal block ● Wall mounting kits and DIN-Rail kits ● Instruction sheet	● 台達 DVS 工業級 PoE+ 分配器 ● RJ45 埠保護蓋 ● 螺絲(M3) ● 4-pin 端子座 ● 壁掛式與軌道式金屬配件 ● 安裝說明	● 台达 DVS 工业级 PoE+ 分配器 ● RJ45 端口保护盖 ● 螺丝(M3) ● 4-pin 端子座 ● 壁挂式与卡轨式金属配件 ● 安装说明 ● 保证卡

EN Operating Voltage	TW 操作電壓	CN 操作电压
● Input Voltage 36 – 57 V_{DC} on RJ45 connector ● Output Power 27Watts / 1.125A(Max) / 24VDC 15.4Watts / 517mA / 24VDC	● 輸入電壓 36 – 57 V_{DC} on RJ45 接頭 ● 輸出功率 27Watts / 1.125A(Max) / 24VDC 15.4Watts / 517mA / 24VDC	● 输入电压 36 – 57 V_{DC} on RJ45 接头 ● 输出功率 27Watts / 1.125A(Max) / 24VDC 15.4Watts / 517mA / 24VDC

EN Ethernet interface connection			TW 乙太網路介面	CN 以太网口
PIN	10/100Base-T(X)	1000Base-T		
1	Rx+	TP0+		
2	Rx-	TP0-		
3	Tx+	TP1+		
4	n.c.	TP2+		
5	n.c.	TP2-		
6	Tx-	TP1-		
7	n.c.	TP3+		
8	n.c.	TP3-		

EN PoE Pin Definition1		TW PoE 腳位定義 1	CN PoE 腳位定义 1
PIN	10/100Base-T(X)	1000Base-T	8-PIN RJ45 
1	Rx+	TP0+	
2	Rx-	TP01--	
3	Tx+	TP1+	
4	Vdc+	TP2+(Vdc+)	
5	Vdc+	TP2-(Vdc+)	
6	Tx-	TP1-	
7	Vdc-	TP3+(Vdc-)	
8	Vdc-	TP3-(Vdc-)	

EN PoE Pin Definition2		TW PoE 腳位定義 2	CN PoE 腳位定义 2
PIN	10/100Base-T(X)	1000Base-T	8-PIN RJ45 
1	Rx+(Vdc+)	TP0+(Vdc+)	
2	Rx-(Vdc+)	TP01(Vdc+)	
3	Tx+(Vdc-)	TP1+(Vdc-)	
4	n.c.	TP2+	
5	n.c.	TP2-	
6	Tx-(Vdc-)	TP1-(Vdc-)	
7	n.c.	TP3+	
8	n.c.	TP3-	

EN Mechanical Characteristics	TW 實體特性	CN 实体特性
● Case IP30 metal case ● Dimension(mm) 95(H)x26.1(W)x70(D) ● Weight(g) 250	● 外殼 IP30 金屬殼 ● 尺寸(mm): 95(H)x26.1(W)x70(D) ● 重量(公克) 250	● 外壳 IP30 金属壳 ● 尺寸(mm): 95(H)x26.1(W)x70(D) ● 重量(公克) : 250