

Digitized Automation for a Changing World

Delta Electric Servo Press AM-ESP S Series

Precise · Robust · Stable

- High repeatability and multiple strokes
- Precise press and flexible control
- Seamless hardware and software integration for high efficiency
- Multiple processes adaptable to changeovers
- Multiple machine connection and remote control
- Robust design






Delta Electric

Precise. Fast.

In modern industries, diversification, short lead time, multiple functions and customization are demanded for manufacturing in all fields. Since 2000, Delta has been working on the development of servo presses for the processing of fans, motors, network appliances, automobiles, electronics assembly, and more. With in-depth know-how and real experience, Delta presents this new electric servo press for more efficient, energy-saving manufacturing.

Delta's electric servo press features precise control of press force and processes for high efficiency and energy savings. It requires no conventional press parts such as flywheel, pneumatic cylinder, motor, clutch, or others, and can solve noise pollution, oil leakage, oil seal

Servo Press AM-ESP S Series



Servo Press Stable and Reliable



failure, inconsistent press force and other pneumatic or hydraulic press issues that automobile and electronic component manufacturers have experienced in the past.

All of the key components are designed and manufactured by Delta for seamless integration, stable operation, high production efficiency and provided as a one-stop-shop service. When connected with equipment management platforms, the electric servo press supports data exchange for monitoring in real time and flexible changeover on smart automated production lines. It helps customers increase their yield rates and competitiveness.

Features



Precise Force and Position Control



Multiple Control Modes



Safe and Energy-saving



User-friendly Interface



Remote Control for Fast Execution



Comprehensive PC-based Software for High Efficiency

Applications



Vehicle Charging Devices



Metal Parts



Electronic and Electrical Appliance Components



Industrial Robots



Features

Precise Force and Position Control

Applies servo motors to drive low-backlash ballscrew and tool holder for high repeatability and precision


- Press force: 500 ~ 5,000 kgf
- Integral casting and used with Delta's servo motors for high dynamic load capacity
- Fast control mode switching and precise control of press force, position, time required, and settings

Multiple Control Modes: Real-time Control and Monitoring

Reduces defect rates and elevates forming efficiency for specific products


Position Mode

Enables the press punch to move downwards to a defined absolute position and avoids over-press force




Force Mode

Makes the press punch press to a defined force and ensures the precise press position




Distance Mode

Allows the press punch to press a workpiece to a relative distance and ensures the precise press force and position



● Force Distance Mode ♠ .


Presses to a relative distance with a constant force and ensures the precise press position



- For Powder and Fluid Forming


Force Position Mode

Presses to an absolute position with a constant force



Multiple Mode

All of the modes mentioned above can be applied interchangeably per users' demands



Safe and Energy-Saving

- Emergency stop with a push button avoids damages to the machine or workpieces and ensures operational safety
- Energy-saving control system for real-time monitoring and alarms
- Easy maintenance and lifespan extension
- Built-in servo motors reduces power consumption
- Cost saving with no conventional pressing parts required



User-Friendly Interface

- Intuitive operation interface
- Real-time pressing records and data upload
- Production data acquisition and tracking
- Data visualization with statistical reports and graphs output
- Data upload to the Cloud for remote management via manufacturing execution system (MES)





Remote Control for Fast Execution

Data upload to the manufacturing execution system (MES) via the built-in Ethernet communication for efficient and remote management, recording and analysis

Comprehensive PC-Based Software for High Efficiency (Optional)

Real-time Monitoring on Pressing Status

- Real-time display of pressing curves and status, sensor values and statistics
- Production visualization (productivity, yield rates, and more) to enhance management efficiency

Comprehensive Process Settings

- Pressing parameter and condition settings
- Pressing recipes export for the use of other machines or saving as samples

Data Analysis and Statistical Reports Output

- Pressing data, records and charts
- Statistical data calculation for batch production
- Statistical reports and graphs output for tracking





Model Information

<u>AM - ESP - S 001 - 1 0 A T</u>

Category	Product Type	Serial	Max. Press Force	Max. Stroke	Voltage	Accessory	Certification
Advanced Manufacturing	Electric Servo Press	S: Standard	005 = 500 kgf 010 = 1,000 kgf 030 = 3,000 kgf 050 = 5,000 kgf	1 = 100 mm 2 = 200 mm	0=220 V/1 Φ 1=220 V/3 Φ 2=380 V/3 Φ	■ 500 kgf/1,000 kgf Series A: Table Stand / Safety Light Curtain and Fences C: Table Stand E: Safety Light Curtain and Fences G: No need ■ 3,000 kgf/5,000 kgf Series B: Table Stand / Safety Light Curtain and Fences D: Table Stand F: Safety Light Curtain and Fences G: No need	T = TS certified C = CE certified

Specifications

Model Name		AM-ESP-S005-10	AM-ESP-S010-10	AM-ESP-S030-21	AM-ESP-S050-21		
	Max. Press Force (kgf)	500	1,000	3,000	5,000		
	Force Range (kgf)	5~500	10~1,000	30~3,000	50~5,000		
Force	Min Increment / Decrement (kgf)	0.1		1			
Max. Deviation (%)		±1 FS*1					
Spindle Max. Stroke (mm)		10	00	200			
Stroke Min. Increment / Decrement (mm)		0.001					
Max. No-load Speed (mm/s)		166					
Spindle Speed	Max. Press Speed (mm/s)	40*2					
Min. Increment / Decrement (mm/s)		0.001					
Repeatability of Position Control (mm)		± 0.005*3					
Load Capacity of Press Punch (kg)*4		10 100		00			
Power Supply		220 Vac × 1 ф, 10 A 220 Vac × 3 ф, 30 A			3ф, 30А		
Power Cable Length (m)		5					
Pressing Area Dimensions (W×H mm)		325×245 400×450			× 450		
Over-press Protection		Yes					

__: Accessory and Certification (T indicates TS certified, C indicates CE certified)


^{*}Note 1: FS = Full Scale

^{*}Note 2: Pressing speed is altered by pressing value ;

^{*}Note 3: The equipment should be operated under constant temperature and pressure to maintain the precision of press repeatability, not absolute accuracy.

^{*}Note 4: The index is not the breaking retaining force

Dimensions



__: Accessory and Certification (T indicates TS certified, C indicates CE certified)

Ordering Information

Model Name	Max. Press Force (kgf)	Max. Stroke (mm)	Accessory
AM-ESP-S005-10AT		100	Uses the dedicated standard table stand, safety light curtain and fences.
AM-ESP-S005-10CT	500		Uses the dedicated standard table stand.
AM-ESP-S005-10ET			Uses the dedicated safety light curtain and fences.
AM-ESP-S005-10GT			No accessory needed
AM-ESP-S010-10AT	1,000		Uses the dedicated standard table stand, safety light curtain and fences.
AM-ESP-S010-10CT			Uses the dedicated standard table stand.
AM-ESP-S010-10ET			Uses the dedicated safety light curtain and fences.
AM-ESP-S010-10GT			No accessory needed
AM-ESP-S030-21BT		200	Uses the dedicated standard table stand, safety light curtain and fences.
AM-ESP-S030-21DT	3,000		Uses the dedicated standard table stand.
AM-ESP-S030-21FT			Uses the dedicated safety light curtain and fences.
AM-ESP-S030-21GT			No accessory needed
AM-ESP-S050-21BT			Uses the dedicated standard table stand, safety light curtain and fences.
AM-ESP-S050-21DT	F 000		Uses the dedicated standard table stand.
AM-ESP-S050-21FT	5,000		Uses the dedicated safety light curtain and fences.
AM-ESP-S050-21GT			No accessory needed



Optional Accessories

Item Image	Type	Part Number	Dimensions (W×D×H) and Description
6	0.5T/1T Safety Light Curtain and Fences	5811125488	Type 4 Safety Light Curtain 327×540×460 mm
©	3T/5T Safety Light Curtain and Fences	5811125487	Type 4 Safety Light Curtain 580×798×730mm
K	0.5T/1T Standard Table Stand	4277234500	Perfect height for operation 850×600×765 mm
3T/5T Standard Table Stand		4277221200	Perfect height for operation 1,250×800×700mm

Advanced Manufacturing Industrial Automation Business Group

Delta Electronics, Inc.

Chungli Plant 1 No.3, Dongyuan Rd., Zhongli District, Taoyuan City 32063, Taiwan

TEL: 886-3-4526107/FAX: 886-3-4527314

EMAIL: ambu@deltaww.com

