



Digitized Automation for a Changing World

# Delta Power Meter DPM Series



[www.deltaww.com](http://www.deltaww.com)



**DELTA**  
Smarter. Greener. Together.

# Delta Power Meter

## DPM Series

The DPM Series precisely measures various electrical energy and power quality parameters, including power factors, harmonics, and current/voltage unbalance. This series also features a variety of communication protocols for easy integration with critical power systems and monitoring functions to provide power data, off-limit alarms, and history logs.

### Panel Mount Type DPM-C Series



- Real-time data display and easy integration with remote monitoring systems, suitable for general applications in machine rooms

#### Applications

Distribution board | Electrical room |  
Factory/Building energy management system

### DIN Rail Mount Type DPM-D Series



- Easy installation and integration for equipment energy management

#### Applications

High power consuming equipment |  
Electrical equipment cabinet | Enclosure

### Multi-Loop Type DPM-M Series



- Multiple and selective large-scale circuit monitoring with lots of power circuits to save cost

#### Applications


Shopping mall | Dormitory | Telecommunication System

## High Precision Power Measurement

- Precise measurement of bidirectional electrical energy and power parameters, meeting IEC 62053-22 standards


## Built-in Protocols for Easy Integration

- Built-in RS-485 communication port supports Modbus for transmission of all measurement values to the PLCs, PCs and monitoring software




## PC-based Configuration Software

- The power meter configuration software DPMSOFT collects electricity data and sets up meters via Modbus communication, achieving easy power management and analysis



## User-defined Parameter Groups

- Allows user-defined Modbus addresses to multiple corresponding parameters for the host computer to acquire data at one time and enhance efficiency



# Panel Mount Type DPM-C Series

- Suitable for applications in general power systems
- Large LCD displays power data in real time
- A variety of communication protocols for easy integration
- Various power monitoring functions for different applications

## Applications

Distribution board | Electrical room |  
Factory/Building energy management system



## Features

### Multi-Language Display

- Large dot matrix LCD (198x168 dots), high font recognition
- Multi-language display: English (capital and lowercase letters), Chinese, Japanese and other languages



DPM-C530: dot matrix LCD for high recognition display, better than segment LCD display

Ptot 123456.78 kW  
Etot 123456.78 kVARh




### Event Alarms and History Logs

- Keeps max. 2 months of electricity measurement values for analysis;  
up to 17 power parameters selectable for recordings of different time intervals (e.g. recording 17 electricity parameters every 5 minutes for up to 2 months);  
29 types of built-in alarms and up to 500 alarms recording

Interval	0~59 secs.	1~5 mins.	5~60 mins.
<b>Capacity</b>			
<b>Max. Data Types</b>	6	17	17
<b>Max. Storage Time (Days)</b>	7	31	62


## Auto-Recording

- Automatic calculation of monthly energy consumption
- Allows users to setup specific dates for monthly calculation



## Multi-Tariff

- Automatic measurement & calculation of power consumption during a specific time period
- Multiple interval groups setting to measure power consumption at different periods of time



## Ethernet Communication


- Dual Ethernet protocols support Modbus TCP
- Easy serial connection without gateway, no need to occupy communication ports
- Basic settings and data viewing on web page





## WiFi

- WiFi transmission
  - Reduced wiring cost and time
  - High-speed data exchange and data transmission capability (faster than RS-485)
  - Highly secure wireless data exchange
- No wiring limit, reduces cost and manpower for wiring



## Input/Output/Relay

Achieves easier system integration with functions such as anomaly alarms, and connected devices' monitoring & control.



### Digital input

External condition monitoring/input metering/  
setting adjustment



### Digital output

Alarms/pulse (kWh only) calculation








### Relay

Alarms/external devices activation



# DPM-C Series Information

Model	DPM-C530	DPM-C530E	DPM-C532	DPM-C520	DPM-C520W
Product Appearance					
Front Panel Dimensions	96x96 mm	96x96 mm	96x96 mm	96x96 mm	96x96 mm
<b>Accuracy Class</b>					
Active Energy (IEC 62053-22)	Class 0.5S	Class 0.5S	Class 0.5S	Class 0.5S	Class 0.5S
<b>Instantaneous Measurement</b>					
Current	●	●	●	●	●
Voltage	●	●	●	●	●
Frequency	●	●	●	●	●
Active, Reactive and Apparent Power	●	●	●	●	●
Power Factor	●	●	●	●	●
Active, Reactive and Apparent Energy	●	●	●	●	●
<b>Demand Value</b>					
Current	●	●	●		
Power	●	●	●		
Calculation Mode	Fixed Block	Sliding Block/Fixed Block	Sliding Block/Fixed Block		
<b>Power Quality Analysis</b>					
Current/Voltage Unbalance	●	●	●	●	●
Total Harmonic Distortion (Current/Voltage)	●	●	●	●	●
Individual Current/Voltage Harmonics	31 <sup>st</sup>	31 <sup>st</sup>	31 <sup>st</sup>		
<b>Advanced Function</b>					
Max./Min. Instantaneous Values with Timestamp	●	●	●	●	●
Alarm Function	●	●	●	●	●
Alarm Condition	29	29	29	10	10
Alarm Logs	●	●	●		
Data Logs	●	●	●		
User-defined Modbus Address	35	35	35	5	5
Monthly Energy Usage	●	●	●		
Multi-Tariff (Section number)	8	8	8		
Multi-Language UI	Chinese/English/Japanese	Chinese/English/Japanese	Chinese/English/Japanese		
<b>I/O</b>					
Digital Input			4		
Digital Output			2		
Relay					
<b>Communication</b>					
RS-485	●		●	●	●
Ethernet		● (2 ports)			
Modbus	RTU/ASCII	TCP	RTU/ASCII	RTU	RTU/TCP
BACnet MS/TP	●		●		
WiFi (802.11 b/g/n)					●

Model	DPM-C320	DPM-C510	DPM-C501L	DPM-C502
Product Appearance				
Front Panel Dimensions	72x72 mm	96x96 mm	96x96 mm	96x96 mm
<b>Accuracy Class</b>				
Active Energy (IEC 62053-22)	Class 0.5S	Class 0.5	0.5%	0.5%
<b>Instantaneous Measurement</b>				
Current	●	●	●	●
Voltage	●	●	●	●
Frequency	●	●	●	●
Active, Reactive and Apparent Power	●	●	●	●
Power Factor	●	●	●	●
Active, Reactive and Apparent Energy	●	●	●	●
<b>Demand Value</b>				
Current				
Power				●
Calculation Mode				Sliding Block
<b>Power Quality Analysis</b>				
Current/Voltage Unbalance	●		●	●
Total Harmonic Distortion (Current/Voltage)	●		●	●
Individual Current / Voltage Harmonics				31 <sup>st</sup>
<b>Advanced Function</b>				
Max./Min. Instantaneous Values with Timestamp	●		●	●
Alarm Function	●		●	●
Alarm Condition	10		10	10
Alarm Logs				
Data Logs				●
User-defined Modbus Address	5		5	5
Monthly Energy Usage				
Multi-Tariff (Section number)				4
Multi-Language UI				
<b>I/O</b>				
Digital Input			4	4
Digital Output				
Relay			2	2
<b>Communication</b>				
RS-485	●	●	●	●
Modbus	RTU	RTU	RTU	RTU



# Technical Specifications




Model	DPM-C530	DPM-C530E	DPM-C532
<b>Measurement Accuracy</b>			
Current		± 0.5%	
Voltage		± 0.5%	
Active Energy		IEC 62053-22 Class 0.5S	
Reactive Energy		± 1%	
Apparent Energy		± 2%	
Active Power		± 0.5%	
Reactive Power		± 1%	
Apparent Power		± 2%	
Power Factor		± 0.5%	
Frequency		± 0.5%	
<b>Input</b>			
Measuring System Type	1P2W, 1P3W, 3P3W, 3P4W		
Voltage	35 V <sub>AC</sub> ~690 V <sub>AC</sub> (L-L); 20 V <sub>AC</sub> ~400 V <sub>AC</sub> (L-N)		
Current	1A/5A		
Frequency	45~70Hz		
Control Power	AC: 100~240V (max. power consumption 4.6W); DC: 100~300V		
<b>Digital Input</b>			
On Voltage			11~40 V <sub>DC</sub>
Off Voltage			0~4 V <sub>DC</sub>
Input current			≤ 8 mA
Input Resistance			3k Ω
Maximum Frequency			200Hz
Isolation			5kV rms
<b>Digital Output</b>			
Max load voltage			40 V <sub>DC</sub>
Max load current			20 mA
On Resistance			50 Ω max
Frequency for Digital Output			100Hz max
Pulse width for Digital Output			50% duty cycle
Isolation			5kV rms
<b>Data Record</b>			
Max./Min. Value	●	●	●
Alarm Status & Timestamp	●	●	●
Alarm Counting	●	●	●
Alarm Logs	500	500	500
Data Logs	Up to 17 parameters with configurable interval & duration (e.g. 17 parameters for 30 days at 1 minute intervals)		
Customizable Data Logs	●	●	●
<b>Communication</b>			
Protocol (Interface)	Modbus RTU/ASCII (RS-485) BACnet MS/TP (RS-485)	Modbus TCP (Ethernet)	Modbus RTU/ASCII (RS-485) BACnet MS/TP (RS-485)
<b>Mechanical Design</b>			
IP Rating - Front Panel		IP52	
IP Rating - Case		IP20	
Dimensions (W x H x D, mm)	96 x 96 x 95.4	96 x 96 x 127.5	96 x 96 x 127.5
Weight (g)	400	450	450
<b>Operating Environment</b>			
Operating Temperature	-20 °C ~ +60 °C		
Storage Temperature	-30 °C ~ +70 °C		
Relative Humidity	~ 95% RH		
Altitude	Below 2,000 meters		
<b>Electromagnetic Compatibility</b>			
Electrostatic Discharge	IEC 61000-4-2		
Immunity to Radiated Fields	IEC 61000-4-3		
Immunity to Fast Transients	IEC 61000-4-4		
Immunity to Impulse Waves	IEC 61000-4-5		
Conducted Immunity	IEC 61000-4-6		
Immunity to Magnetic Fields	IEC 61000-4-8		
Immunity to Voltage Dips	IEC 61000-4-11		
Radiated Emissions	FCC Part 15, EN 55011 Class A		
Conducted Emissions	FCC Part 15, EN 55011 Class A		
Harmonics Emissions	IEC 61000-3-2		
Flicker Emissions	IEC 61000-3-3		
<b>Certification</b>			
Safety	UL/CE/RCM		UL/CE
Accuracy	IEC 62053-22/CMA		

Model	DPM-C520	DPM-C520W	DPM-C320
<b>Measurement Accuracy</b>			
Current		± 0.5%	
Voltage		± 0.5%	
Active Energy		IEC 62053-22 Class 0.5S	
Reactive Energy		± 1%	
Apparent Energy		± 2%	
Active Power		± 0.5%	
Reactive Power		± 1%	
Apparent Power		± 2%	
Power Factor		± 0.5%	
Frequency		± 0.5%	
<b>Input</b>			
Measuring System Type		1P2W, 1P3W, 3P3W, 3P4W	
Voltage		35 V <sub>AC</sub> ~690 V <sub>AC</sub> (L-L) 20 V <sub>AC</sub> ~400 V <sub>AC</sub> (L-N)	
Current		1A/5A	
Frequency		45~70Hz	
Control Power		AC: 100~240V (max. power consumption 4.6W) DC: 100~300V	
<b>Data Record</b>			
Max. /Min. Value	●	●	●
Alarm Status & Timestamp	●	●	●
Alarm Counting	●	●	●
<b>Communication</b>			
Protocol (Interface)	Modbus RTU (RS-485)	Modbus RTU (RS-485) / Modbus TCP (WiFi, IEEE802.11 b/g/n)	Modbus RTU (RS-485)
<b>Mechanical Design</b>			
Dimensions (W x H x D, mm)	96 x 96 x 95.4	96 x 96 x 95.4	72 x 72 x 107.7
Weight (g)	400	400	250
<b>Operating Environment</b>			
Operating Temperature		-20 °C ~ +60 °C	
Storage Temperature		-30 °C ~ +70 °C	
Relative Humidity		~ 95% RH	
Altitude		Below 2,000 meters	
<b>Electromagnetic Compatibility</b>			
Electrostatic Discharge		IEC 61000-4-2	
Immunity to Radiated Fields		IEC 61000-4-3	
Immunity to Fast Transients		IEC 61000-4-4	
Immunity to Impulse Waves		IEC 61000-4-5	
Conducted Immunity		IEC 61000-4-6	
Immunity to Magnetic Fields		IEC 61000-4-8	
Immunity to Voltage Dips		IEC 61000-4-11	
Radiated Emissions		FCC Part 15, EN 55011 Class A	
Conducted Emissions		FCC Part 15, EN 55011 Class A	
Harmonics Emissions		IEC 61000-3-2	
Flicker Emissions		IEC 61000-3-3	
<b>Certification</b>			
Safety		UL/CE	
Accuracy		IEC 62053-22/CMA	
WiFi		CE/FCC/JRF/ KCC/NCC/NBTC	




Model	DPM-C510	DPM-C501L	DPM-C502
<b>Measurement Accuracy</b>			
Current	± 0.5%	± 0.5%	± 0.5%
Voltage	± 0.5%	± 0.5%	± 0.5%
Active Energy	IEC 62053-22 Class 0.5	± 0.5%	± 0.5%
Reactive Energy	± 2%	± 1%	± 1%
Apparent Energy	± 2%	± 2%	± 2%
Active Power	± 0.5%	± 0.5%	± 0.5%
Reactive Power	± 2%	± 1%	± 1%
Apparent Power	± 2%	± 2%	± 2%
Power Factor	± 0.5%	± 0.5%	± 0.5%
Frequency	± 1%	± 0.5%	± 0.5%
<b>Input</b>			
Measuring System Type	1P2W, 1P3W, 3P3W, 3P4W	1P2W, 1P3W, 3P3W, 3P4W	
Voltage	80 V <sub>AC</sub> ~690 V <sub>AC</sub> (L-L) 50 V <sub>AC</sub> ~400 V <sub>AC</sub> (L-N)	35 V <sub>AC</sub> ~690 V <sub>AC</sub> (L-L) 20 V <sub>AC</sub> ~400 V <sub>AC</sub> (L-N)	
Current	1A/5A	1A/5A	
Frequency	50/60Hz	45~70Hz	
Control Power	AC: 100~240V (max. power consumption 4.6W) DC: 100~300V	AC: 100~240V (max. power consumption 4.6W) DC: 100~300V	
<b>Digital Input</b>			
On Voltage		With build-in power	
Off Voltage			
Input current		≤ 5 mA	
Input Resistance		3k Ω	
Maximum Frequency		20Hz	
Isolation		2.5kV rms	
<b>Relay</b>			
Max output frequency		20 Hz	
Switching current		240 V <sub>AC</sub> at 2Amps, resistive 24 V <sub>DC</sub> at 2Amps, resistive	
Isolation		2.5kV rms	
<b>Data Record</b>			
Max./Min. Value		●	●
Alarm Status & Timestamp		●	●
Alarm Counting		●	●
Alarm Logs			
Data Logs			Fixed 4 parameters with configurable interval & duration (e.g. 4 parameters for 7 days at 1 minute intervals)
<b>Communication</b>			
Protocol (Interface)	Modbus RTU (RS-485)	Modbus RTU (RS-485)	
<b>Mechanical Design</b>			
IP Rating - Front Panel	IP52	IP52	
IP Rating - Case	IP20	IP20	
Dimensions (W x H x D, mm)	96 x 96 x 98.1	96 x 96 x 95.4	
Weight (g)	350	400	400
<b>Operating Environment</b>			
Operating Temperature	-20 °C ~ +60 °C	-20 °C ~ +50 °C	
Storage Temperature	-30 °C ~ +70 °C	-30 °C ~ +60 °C	
Relative Humidity	~ 95% RH	~ 95% RH	
Altitude	Below 2,000 meters	Below 2,000 meters	
<b>Electromagnetic Compatibility</b>			
Electrostatic Discharge	IEC 61000-4-2	IEC 61000-4-2	
Immunity to Radiated Fields	IEC 61000-4-3	IEC 61000-4-3	
Immunity to Fast Transients	IEC 61000-4-4	IEC 61000-4-4	
Immunity to Impulse Waves	IEC 61000-4-5	IEC 61000-4-5	
Conducted Immunity	IEC 61000-4-6	IEC 61000-4-6	
Immunity to Magnetic Fields	IEC 61000-4-8	IEC 61000-4-8	
Immunity to Voltage Dips	IEC 61000-4-11	IEC 61000-4-11	
Radiated Emissions	FCC Part 15, EN 55011 Class A	FCC Part 15 EN 55011 Class A	
Conducted Emissions	FCC Part 15, EN 55011 Class A	FCC Part 15 EN 55011 Class A	
Harmonics Emissions	IEC 61000-3-2	IEC 61000-3-2	
Flicker Emissions	IEC 61000-3-3	IEC 61000-3-3	
<b>Certification</b>			
Safety	UL/CE		
Accuracy	IEC 62053-22/CMA		CMA

# Dimensions




DPM-C530  
DPM-C520  
DPM-C520W




DPM-C530E




DPM-C532




**DPM-C320**



**DPM-C510**



**DPM-C501L  
DPM-C502**





# DIN Rail Mount Type DPM-D Series

- Easy installation and integration for various equipment
- Applicable to general energy management systems
- Multiple energy measurement functions for different applications

## Applications



High power consuming equipment |  
Electrical equipment cabinet | Enclosure



## Features


### Multi-Tariff

- Automatic measurement & calculation of power consumption during a specific time period
- Multiple interval groups setting to measure power consumption at different periods of time



### Pulse Output

- DPM-DA510/D530: Pulse output by active energy/reactive energy (import/export)
- Frequency divider: 1 ~ 9,999
- Pulse width: 0 ~ 5,000 ms (0 = 50% duty cycle)



Pulse output 40 V<sub>DC</sub>/50 mA  
Per 0.1 kWh (default)

## Data Recording

- User-defined time intervals for recording (Units: day/hour/min./sec.)
- Max. 50 parameters recording
- Max. 16 alarm conditions and max. 16 alarms recording


Recorded items vs. Record duration (at 1 minute intervals)

Parameter(s)	Recording Days
1	90
7	30
20	12


## Demand Calculation

- Defines time intervals (default: 15 mins.)
- Demand calculation methods: Sliding block/fixed block
- Calculates the max. demand value/time in each tariff period

### Sliding Block



### Fixed Block




## Automatic Wiring Correction (DPM-DA530)

- Automatic wiring correction via algorithm to save manpower for on-site re-wiring
- Fixes phase wiring errors and adjusts power flow direction

\* Refer to product manual for function restrictions

### Operation Process



## DPM-D Series Information




Model	DPM-D520I	DPM-DA530	DPM-DA510
Product Appearance			
<b>Accuracy Class</b>			
Active Energy (IEC 62053-22)	0.5%	0.5%	0.5%
<b>Instantaneous Measurement</b>			
Current	●	●	●
Voltage	●	●	●
Frequency	●	●	●
Active, Reactive and Apparent Power	●	●	●
Power Factor	●	●	●
Active, Reactive and Apparent Energy	●	●	●
Phasor Diagram (Current/Voltage)		●	●
<b>Current Measurement</b>			
Direct Measurement (Current Range)	63A		
Via External CT (Current Range)		1A/5A	1A/5A
<b>Demand Value</b>			
Current	●	●	
Power	●	●	
Calculation Mode	Fixed Block	Sliding Block/Fixed Block	
<b>Power Quality Analysis</b>			
Current/Voltage Unbalance	●	●	
Total Harmonic Distortion (Current/Voltage)	●	●	
Individual Current/Voltage Harmonics	31 <sup>st</sup>		
<b>Advanced Function</b>			
Max./Min. Instantaneous Values with Timestamp	●	●	
Alarm Function	●	●	
Alarm Condition	29	16	
Alarm Logs	●	●	
Data Logs	●	●	
User-defined Modbus Address	35	20	
Monthly Energy Usage	●		
Multi-Tariff (Section number)	8	8	
Auto Wiring Correction		●	
CO <sub>2</sub> Emission		●	
<b>I/O</b>			
Pulse Output		1	1
<b>Communication</b>			
RS-485	●	●	●
Modbus	RTU/ASCII	RTU	RTU

# Technical Specifications



Model	DPM-D520I	DPM-DA530	DPM-DA510
<b>Measurement Accuracy</b>			
Current	± 0.5%	± 0.5%	± 0.5%
Voltage	± 0.5%	± 0.5%	± 0.5%
Active Energy	± 0.5%	± 0.5%	± 0.5%
Reactive Energy	± 1%	± 2%	± 2%
Apparent Energy	± 2%	± 2%	± 2%
Active Power	± 0.5%	± 0.5%	± 0.5%
Reactive Power	± 1%	± 2%	± 2%
Apparent Power	± 2%	± 2%	± 2%
Power Factor	± 0.5%	± 0.5%	± 0.5%
Frequency	± 0.5%	± 0.5%	± 0.5%
<b>Input</b>			
Measuring System Type	1P2W, 1P3W, 3P3W, 3P4W		
Voltage	35 V <sub>AC</sub> ~690 V <sub>AC</sub> (L-L) 20 V <sub>AC</sub> ~400 V <sub>AC</sub> (L-N)		35 V <sub>AC</sub> ~600 V <sub>AC</sub> (L-L) 20 V <sub>AC</sub> ~350 V <sub>AC</sub> (L-N)
Current	63A		1A/5A
Frequency	45~70 Hz		45~65 Hz
Control Power	AC: 80~265V (Max. Power Consumption 4.6 W) DC: 100~300V		AC: 100~240V ( Max. Power Consumption 3W) DC: 100~250V
<b>Pulse Output</b>			
Max load voltage			40 V <sub>DC</sub>
Max load current			50 mA
Frequency for Digital Output			1 kHz max
Pulse width for Digital Output			50% duty cycle
Isolation			2.5kV rms
<b>Data Record</b>			
Max./Min. Value	●	●	
Alarm Status & Timestamp	●	●	
Alarm Counting	●	●	
Alarm Logs	500	16	
Data Logs	Up to 17 parameters with configurable interval & duration (e.g. 17 parameters for 30 days at 1 minute intervals)	Up to 50 parameters with configurable interval & duration (e.g. 7 parameters for 30 days at 1 minute intervals)	
Customizable Data Logs	●	●	
<b>Communication</b>			
Protocol (Interface)	Modbus RTU/ASCII (RS-485)	Modbus RTU (RS-485)	Modbus RTU (RS-485)
<b>Mechanical Design</b>			
IP Rating - Case	IP20		IP20
Dimensions (WxHxD, mm)	126x90x67.4		72x87.5x58.7
Weight (g)	600		195
<b>Operating Environment</b>			
Operating Temperature	-20°C~+60°C		0°C~+60°C
Storage Temperature	-30°C~+70°C		-10°C~+70°C
Relative Humidity			~95% RH
Altitude			Below 2,000 meters
<b>Electromagnetic Compatibility</b>			
Electrostatic Discharge		IEC 61000-4-2	
Immunity to Radiated Fields		IEC 61000-4-3	
Immunity to Fast Transients		IEC 61000-4-4	
Immunity to Impulse Waves		IEC 61000-4-5	
Conducted Immunity		IEC 61000-4-6	
Immunity to Magnetic Fields		IEC 61000-4-8	
Immunity to Voltage Dips		IEC 61000-4-11	
Radiated Emissions		FCC Part 15, EN 55011 Class A	
Conducted Emissions		FCC Part 15, EN 55011 Class A	
Harmonics Emissions		IEC 61000-3-2	
Flicker Emissions		IEC 61000-3-3	
<b>Certification</b>			
Safety	CE/RCM		CE
Accuracy	CMA		

# Dimensions

**DPM-DA530  
DPM-DA510**



**DPM-D520I**





# Multi-loop Type DPM-M Series

- Multiple and selective circuit monitoring reduces the use of power meters in large-scale areas
- Suitable for applications with lots of power circuits to save cost
- AC/DC measurement

## Applications

Shopping mall | Dormitory | Telecommunication System




## Features

### Scalable Multi-Loop Configuration (DPM-MA3222)

- Dual main circuits with isolation for connection to different power systems
- Each main circuit connects 4 subcircuits; configures a total of 8 circuits (three-phase) or 24 circuits (single-phase)
- Subcircuit can be set to three-phase, single-phase, or three-phase & single-phase modes

Multi-loop  
AC Power Meter  
DPM-MA3222



## I/O Configuration (DPM-MA3222)


- Various I/O types for control and integration with peripheral devices



I/O Type	Qty.	Functions
Relay Output (RO)	4	<ul style="list-style-type: none"> <li>• 5A/250V<sub>AC</sub>, 5A/30V<sub>DC</sub></li> <li>• Alarm linkage: Hi/Lo/Hi hold/Lo hold</li> </ul>
Digital Input (DI)	2	<ul style="list-style-type: none"> <li>• Demand calculation trigger/stop</li> <li>• Record clearing: demand, max. demand, energy, max./min. value</li> <li>• Relay homing</li> </ul>
Pulse Output (PO)	1	<ul style="list-style-type: none"> <li>• 30V<sub>DC</sub>, 30mA</li> <li>• Active/Reactive power output of any circuit</li> </ul>

## Multi-Loop DC Measurement (DPM-MA1121)

- Supports max. 5 DC circuits
- Suitable for telecommunication, green energy, energy storage applications
- Dedicated power supply for Hall sensor (optional)



### Multi-loop DC Power Meter DPM-MA1121



### Hall Current Transformer (CT) Power Supply DPM-PS01



- Input voltage: 36~72V<sub>DC</sub>
- Output voltage: ±15V<sub>DC</sub>
- Output current: ±100mA

# DPM-M Series Information




Model	DPM-MA3222	DPM-MA1121
Product Appearance		
<b>Accuracy Class</b>		
Active Energy	0.5%	0.5%
<b>Circuit Qty.</b>		
3-Phase Measurement	8	
Single-Phase Measurement	24	5
<b>Instantaneous Measurement</b>		
Current	●	●
Voltage	●	●
Frequency	●	
Active power	●	●
Reactive and Apparent Power	●	
Power Factor	●	
Active Energy	●	●
Reactive and Apparent Energy	●	
<b>Demand Value</b>		
Current	●	
Power	●	
Calculation Mode	Sliding Block/Fixed Block	
<b>Power Quality Analysis</b>		
Current/Voltage Unbalance	●	
Total Harmonic Distortion (Current/Voltage)	●	
Individual Current/Voltage Harmonics	31 <sup>st</sup>	
<b>Advanced Function</b>		
Max./Min. Instantaneous Values with Timestamp	●	
Alarm Function	●	
Alarm Condition	48	
Data Logs	●	●
User-defined Modbus Address	80	20
<b>I/O</b>		
Digital Input	2	
Relay	4	
Pulse Output	1	
<b>Communication</b>		
RS-485	●	●
Modbus	RTU	RTU

# Technical Specifications




Model	DPM-MA3222	DPM-MA1121
<b>Measurement Accuracy</b>		
Current	± 0.5%	± 0.5%
Voltage	± 0.5%	± 0.5%
Active Energy	± 0.5%	± 0.5%
Reactive Energy	± 2%	N/A
Apparent Energy	± 2%	N/A
Active Power	± 0.5%	± 0.5%
Reactive Power	± 2%	N/A
Apparent Power	± 2%	N/A
Power Factor	± 0.5%	N/A
Frequency	± 0.5%	N/A
<b>Input</b>		
Measuring System Type	1P2W, 1P3W, 3P3W, 3P4W	1P2W
Voltage	35 V <sub>AC</sub> ~600 V <sub>AC</sub> (L-L) 20 V <sub>AC</sub> ~400 V <sub>AC</sub> (L-N)	≤100 V <sub>DC</sub>
Current	Main: 5A Subcircuit: 333mV	±4 V <sub>DC</sub> (Hall CT)
Frequency	45~65Hz	
Control Power	AC: 100~240V (max. power consumption 15W) DC: 100~250V	DC: 20~56V (max. power consumption 4W)
<b>Digital Input</b>		
On Voltage	0~1 V <sub>DC</sub>	
Off Voltage	10~12 V <sub>DC</sub>	
Input current	≤ 3.5mA	
Input Resistance	1M Ω	
Maximum Frequency	50Hz	
Isolation	3.5kV rms	
<b>Relay</b>		
Max output frequency	10Hz	
Switching current	250 V <sub>AC</sub> at 5.0 Amps, resistive 30 V <sub>DC</sub> at 5.0 Amps, resistive	
Isolation	2.5kV rms	
<b>Pulse Output</b>		
Max load voltage	30 V <sub>DC</sub>	
Max load current	30mA	
Frequency for Digital Output	40Hz max	
Pulse width for Digital Output	50% duty cycle	
Isolation	2.5kV rms	
<b>Data Record</b>		
Max./Min. Value	●	●
Data Logs	Up to 86 parameters with configurable interval & duration (e.g. 40 parameters for 7 days at 1 minute Intervals)	Up to 21 parameters with configurable interval & duration (e.g. 20 parameters for 6 days at 1 minute Intervals)
Customizable Data Logs	●	●
<b>Communication</b>		
Protocol (Interface)	Modbus RTU (RS-485)	Modbus RTU (RS-485)
<b>Mechanical Design</b>		
IP Rating - Case		IP20
Dimensions (WxHxD, mm)	199x118x77	54x81x65.5
Weight (g)	750	185
<b>Operating Environment</b>		
Operating Temperature		0°C~+60°C
Storage Temperature		-10°C~+70°C
Relative Humidity		~95% RH
Altitude		Below 2,000 meters
<b>Electromagnetic Compatibility</b>		
Electrostatic Discharge		IEC 61000-4-2
Immunity to Radiated Fields		IEC 61000-4-3
Immunity to Fast Transients		IEC 61000-4-4
Immunity to Impulse Waves		IEC 61000-4-5
Conducted Immunity		IEC 61000-4-6
Immunity to Magnetic Fields		IEC 61000-4-8
Immunity to Voltage Dips		IEC 61000-4-11
Radiated Emissions		FCC Part 15, EN 55011 Class A
Conducted Emissions		FCC Part 15, EN 55011 Class A
Harmonics Emissions		IEC 61000-3-2
Flicker Emissions		IEC 61000-3-3
<b>Certification</b>		
Safety		CE

# Dimensions

**DPM-MA3222**



**DPM-MA1121**








# Current Transformer (CT)

- Accessories for current measurement, suitable for all types of power meters
- Proportionally transforms high circuit current into low current (or low voltage) signals for current measurement

## Applications

Matches with all types of power meters to transform high current into measurable low current (voltage)

## Product Information (Refer to Ordering Information for more details)

Type	Model	Features
<b>Solid Core CT</b> 	<b>DCT-MC</b>	<ul style="list-style-type: none"> <li>• Installation through the CT core</li> <li>• Applicable to new system configuration</li> </ul>
<b>Compact Split Core CT</b> 	<b>DCT-CS</b>	<ul style="list-style-type: none"> <li>• Compact size, easy to install/dismantle by opening the split top</li> <li>• Suitable for various applications</li> </ul>
	<b>DCT-MV</b>	
<b>Split Core CT</b> 	<b>DCT-S</b>	<ul style="list-style-type: none"> <li>• Easy to install/dismantle by opening the split top</li> <li>• Complies with safety certifications</li> </ul>

# Ordering Information

## Panel Mount Type Power Meter

Model	Functions (Refer to Technical Specs. for details)	Front Panel Dimensions (mm)	Current Measurement	I/O	Communication	Certifications
Advanced Type	DPM-C530	96 x 96	Through external CT (secondary side): 1 A/5A	4DI/2DO	RS-485 (Modbus/BACNet MS/TP)	CE/UL/RCM
	DPM-C530E				Ethernet x2 (Modbus)	CE/UL
	DPM-C532				RS-485 (Modbus/BACNet MS/TP)	CE/UL
	DPM-C502				RS-485 (Modbus)	
Standard Type	DPM-C520	96 x 96	Through external CT (secondary side): 1 A/5A	4DI/2RO	RS-485 (Modbus)	CE/UL
	DPM-C520W	72 x 72			Wifi (802.11 b/g/n)	
	DPM-C320				RS-485 (Modbus)	
	DPM-C501L	96 x 96			RS-485 (Modbus)	
Basic Type	DPM-C510	96 x 96			RS-485 (Modbus)	CE/UL

## DIN Rail Mount Type Power Meter

Model	Functions (Refer to Technical Specs. for details)	Current Measurement	I/O	Communication	Certifications
Advanced Type	DPM-D520I	Direct measurement: 63A	1PO	RS-485 (Modbus)	CE
	DPM-DA530	Through external CT (secondary side): 1A/5A			
Basic Type	DPM-DA510				

## Multi-Loop Type Power Meter

Model	Functions (Refer to Technical Specs. for details)	Current Measurement	I/O	Communication	Certifications
AC Meas.	DPM-MA3222	Through external CT • Main circuit: 5A (secondary side) • Subcircuit: 333 mV (secondary side)	2DI 4RO 1PO	RS-485 (Modbus)	CE
DC Meas.	DPM-MA1121	Through Hall Sensor			

## Solid Core CT

Model	Certification	Primary Current	Secondary Current	Max. Load	Measurement Accuracy (PF=1)	Dimensions (Unit: mm)
DCT-MC010-5	-	100A	5A	1.5VA	1%	Outer: 80x60x38 Inner: 20x30.5
DCT-MC020-5	-	200A	5A	3.75VA	0.5%	
DCT-MC030-5	-	300A	5A	5VA	0.5%	Outer: 98x74.5x43 Inner: 42x42
DCT-MC040-5	-	400A	5A	7.5VA	0.5%	
DCT-MC050-5	-	500A	5A	5VA	0.5%	Outer: 127x103x45 Inner: 51x61
DCT-MC060-5	-	600A	5A	10VA	0.5%	

## Compact Split Core CT

Model	Certification	Primary Current	Secondary Current	Wiring Length	Measurement Accuracy (PF=1)	Dimensions (Unit: mm)
DCT-CS010-5	-	100A	5A	1,000 mm	1%	Outer: 66.8x49.8x34.2 Inner: 23.8x25.2
DCT-CS020-5	-	200A	5A	1,000 mm	1%	
DCT-CS030-5	-	300A	5A	1,000 mm	1%	
DCT-CS040-5	-	400A	5A	1,000 mm	1%	Outer: 85x69x42.5 Inner: 36.5x36.5
DCT-CS050-5	-	500A	5A	1,000 mm	1%	
DCT-CS060-5	-	600A	5A	1,000 mm	1%	
DCT-MV005-3	CE	5A	333 mV	1,200 mm	1%	Outer: 30.8x28.8x42.8 Inner: Φ10.2
DCT-MV060-3	CE	60A		1,200 mm	0.5%	Outer: 30.3x33.9x49 Inner: Φ16.1
DCT-MV100-3	CE	100A		1,200 mm	0.5%	
DCT-MV200-3	CE	200A		1,200 mm	0.5%	Outer: 53.3x40.2x70 Inner: Φ24.1
DCT-MV300-3	CE	300A		1,200 mm	0.5%	Outer: 67x42.8x83 Inner: Φ24.1
DCT-MV400-3	CE	400A		1,200 mm	0.5%	

## Split Core CT

Model	Certification	Primary Current	Secondary Current	Max. Load	Measurement Accuracy (PF=1)	Dimensions (Unit: mm)
DCT-S201B	UL	100A	5A	1.0 VA	1.0%	Outer: 90x40x110 Inner: 30x20
DCT-S211B	UL	200A	5A	1.0 VA	0.5%	
DCT-S221B	UL	300A	5A	1.5 VA	0.5%	
DCT-S231B	UL	400A	5A	1.5 VA	0.5%	Outer: 115x37x159 Inner: 80x50
DCT-S241B	UL	500A	5A	2.5 VA	0.5%	
DCT-S251B	UL	600A	5A	2.5 VA	0.5%	
DCT-S261B	UL	750A	5A	2.5 VA	0.5%	
DCT-S2C1B	UL	800A	5A	3.75 VA	0.5%	
DCT-S271B	UL	1,000A	5A	5 VA	0.5%	
DCT-S301C	CE	100A	5A	1.5VA	1.0%	Outer: 89x40x115 Inner: 32x21
DCT-S211C	CE	200A	5A	1.0VA	0.5%	
DCT-S221C	CE	300A	5A	1.5 VA	0.5%	
DCT-S231C	CE	400A	5A	2.5 VA	0.5%	
DCT-S241C	CE	500A	5A	2.5 VA	0.5%	Outer: 116x51x145 Inner: 80x50
DCT-S251C	CE	600A	5A	2.5 VA	0.5%	
DCT-S261C	CE	750A	5A	2.5 VA	0.5%	
DCT-S271C	CE	1,000A	5A	5 VA	0.5%	
DCT-S281C	CE	1,500A	5A	7.5 VA	0.5%	Outer: 146x51.6x196 Inner: 80x122
DCT-S291C	CE	2,000A	5A	10 VA	0.5%	Outer: 186x67x250 Inner: 81x160.5
DCT-S2A1C	CE	2,500A	5A	15 VA	0.5%	
DCT-S2B1C	CE	3,000A	5A	20 VA	0.5%	

## Hall Sensor Power Supply

Model	Input Voltage		Output		Ripple & Noise (mVp-p, Typ./Max.)	Efficiency (% , @ Full load)	Dimensions (mm)
	Normal (V <sub>DC</sub> , Range)	Max. (V <sub>DC</sub> )	Voltage (V <sub>DC</sub> )	Current (mA, Max./Min.)			
DPM-PS01	48 (36~72)	80	±15	±100/±5	40/75	80	65.5x26x81



Smarter. Greener. Together.

## Industrial Automation Headquarters

### Taiwan: Delta Electronics, Inc.

Taoyuan Technology Center  
No.18, Xinglong Rd., Taoyuan District,  
Taoyuan City 33068, Taiwan  
TEL: +886-3-362-6301 / FAX: +886-3-371-6301

## Asia

### China: Delta Electronics (Shanghai) Co., Ltd.

No.182 Minyu Rd., Pudong Shanghai, P.R.C.  
Post code : 201209  
TEL: +86-21-6872-3988 / FAX: +86-21-6872-3996  
Customer Service: 400-820-9595

### Japan: Delta Electronics (Japan), Inc.

Industrial Automation Sales Department  
2-1-14 Shibadaimon, Minato-ku  
Tokyo, Japan 105-0012  
TEL: +81-3-5733-1155 / FAX: +81-3-5733-1255

### Korea: Delta Electronics (Korea), Inc.

1511, 219, Gasan Digital 1-Ro., Geumcheon-gu,  
Seoul, 08501 South Korea  
TEL: +82-2-515-5305 / FAX: +82-2-515-5302

### Singapore: Delta Energy Systems (Singapore) Pte Ltd.

4 Kaki Bukit Avenue 1, #05-04, Singapore 417939  
TEL: +65-6747-5155 / FAX: +65-6744-9228

### India: Delta Electronics (India) Pvt. Ltd.

Plot No.43, Sector 35, HSIIDC Gurgaon,  
PIN 122001, Haryana, India  
TEL: +91-124-4874900 / FAX: +91-124-4874945

### Thailand: Delta Electronics (Thailand) PCL.

909 Soi 9, Moo 4, Bangpoo Industrial Estate (E.P.Z),  
Pattana 1 Rd., T.Phraksa, A.Muang,  
Samutprakarn 10280, Thailand  
TEL: +66-2709-2800 / FAX: +66-2709-2827

### Australia: Delta Electronics (Australia) Pty Ltd.

Unit 20-21/45 Normanby Rd., Notting Hill Vic 3168, Australia  
TEL: +61-3-9543-3720

## Americas

### USA: Delta Electronics (Americas) Ltd.

5101 Davis Drive, Research Triangle Park, NC 27709, U.S.A.  
TEL: +1-919-767-3813 / FAX: +1-919-767-3969

### Brazil: Delta Electronics Brazil

Rua Itapeva, 26 - 3º, andar Edifício Itapeva,  
One - Bela Vista 01332-000 - São Paulo - SP - Brazil  
TEL: +55-12-3932-2300 / FAX: +55-12-3932-237

### Mexico: Delta Electronics International Mexico S.A. de C.V.

Gustavo Baz No. 309 Edificio E PB 103  
Colonia La Loma, CP 54060  
Tlalnepantla, Estado de México  
TEL: +52-55-3603-9200

## EMEA

### EMEA Headquarters: Delta Electronics (Netherlands) B.V.

Sales: Sales.IA.EMEA@deltaww.com  
Marketing: Marketing.IA.EMEA@deltaww.com  
Technical Support: iatechnicalsupport@deltaww.com  
Customer Support: Customer-Support@deltaww.com  
Service: Service.IA.emea@deltaww.com  
TEL: +31(0)40 800 3900

### BENELUX: Delta Electronics (Netherlands) B.V.

Automotive Campus 260, 5708 JZ Helmond, The Netherlands  
Mail: Sales.IA.Benelux@deltaww.com  
TEL: +31(0)40 800 3900

### DACH: Delta Electronics (Netherlands) B.V.

Coesterweg 45, D-59494 Soest, Germany  
Mail: Sales.IA.DACH@deltaww.com  
TEL: +49(0)2921 987 0

### France: Delta Electronics (France) S.A.

ZI du bois Challand 2, 15 rue des Pyrénées,  
Lisses, 91090 Evry Cedex, France  
Mail: Sales.IA.FR@deltaww.com  
TEL: +33(0)1 69 77 82 60

### Iberia: Delta Electronics Solutions (Spain) S.L.U

Ctra. De Villaverde a Vallecas, 265 1º Dcha Ed.  
Hormigueras – P.I. de Vallecas 28031 Madrid  
TEL: +34(0)91 223 74 20

Carrer Llacuna 166, 08018 Barcelona, Spain

Mail: Sales.IA.Iberia@deltaww.com

### Italy: Delta Electronics (Italy) S.r.l.

Via Meda 2-22060 Novedrate(CO)  
Piazza Grazioli 18 00186 Roma Italy  
Mail: Sales.IA.Italy@deltaww.com  
TEL: +39 039 8900365

### Russia: Delta Energy System LLC

Vereyskaya Plaza II, office 112 Vereyskaya str.  
17 121357 Moscow Russia  
Mail: Sales.IA.RU@deltaww.com  
TEL: +7 495 644 3240

### Turkey: Delta Greentech Elektronik San. Ltd. Sti. (Turkey)

Şerifali Mah. Hendem Cad. Kule Sok. No:16-A  
34775 Ümraniye – İstanbul  
Mail: Sales.IA.Turkey@deltaww.com  
TEL: + 90 216 499 9910

### MEA: Eltek Dubai (Eltek MEA DMCC)

OFFICE 2504, 25th Floor, Saba Tower 1,  
Jumeirah Lakes Towers, Dubai, UAE  
Mail: Sales.IA.MEA@deltaww.com  
TEL: +971(0)4 2690148